# **Technical data sheet**


Clamp clip 2056, U-foot, single, metal pressure trough, A2

### Item number: 1188434





Clamp clip with U-foot, metal pressure trough with rounded edges to protect the cable. For vertical and horizontal mounting of 1 single cable on a C-profile rail. For slot width 18–22 mm. With 1-start screw thread on pressure trough, universal hexagonal screw head WAF10, with slot and cross recess. Suitable for mounting indoors and outdoors. We recommend the use of a counter-trough.



#### Master data

Item number	1188434
Туре	BS-U1-M-76 A2
Description 1	Clamp clip 2056
Manufacturer	OBO
Dimension	70-76mm
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	25
Unit of quantity	Piece
Weight	17.568 kg
Weight unit	kg/100 pc.
U U	


# **Technical data sheet**

Clamp clip 2056, U-foot, single, metal pressure trough, A2

### Item number: 1188434



#### Dimensions



Length	25 mm
Width	82 mm
Height	108 mm
Plate thickness	2.5 mm
Dimension A	25 mm
Dimension B	82 mm
Dimension C	37 mm
Dimension G (mm)	M8
Dimension H	108 mm
Dimension L	43 mm
Dimension t	2.5 mm

**Technical data** 

1
76 mm
70 mm
22 mm
18 mm
M8
yes
37 mm
5 Nm
yes
Profile rail
10 mm
76 mm
70 mm
Untreated
Rustproof steel