Technical data sheet

PYROPLUG® MagicBox, three-sided, interior height 60 mm



Item number: 7204046



Fire protection box as insulation system, made of single-part stainless steel housing with intumescent fire protection inlays. Can be used in walls, on raw floors, beneath system floors and as insulation of rising sections in ceilings. Interior can be fully assigned with installations. For interior application. Closure of the residual openings with PYROSIT® NG fire protection foam, particularly simple for difficult geometries. CE-labelled construction product with general type approval. Fire resistance class El90 (fire-resistant). Including graphite strip.

(€

A2

Stainless steel

2E

Bright, treated

Master data

Item number	7204046
Туре	PMB 650-3 A2
Description 1	Fire Protection Box 3-sided
Description 2	with intumescending inlays
Available from	04.10.2022
Manufacturer	OBO
Dimension	300x523x116
Material	Stainless steel
Surface	Bright, treated
Surface standard	
Smallest sales unit	1
Unit of quantity	Piece
Weight	459.7 kg
Weight unit	kg/100 pc.

Technical data sheet

PYROPLUG® MagicBox, three-sided, interior height 60 mm



Item number: 7204046



	data

Fire protection version	Box body
Shape	Rectangular
Accessories required	yes
Internal height	65 mm
Internal width	505 mm