

Technical data sheet

Pressure clip for 10 cables

Item number: 2204991



Standard version for general use, e.g. on intermediate ceilings and partition walls.

Clamping height 9 mm – with spacer 13 mm.

Fastening hole: 6 mm Ø.

Steingraue Ausführung: Flammwidrige Ausführung, speziell für die Verwendung in Zwischendecken.

Thermopl. Polyester, steingrau RAL 7030, flammwidrig nach VDE 0471/DIN IEC 695 Teil 2-1, Prüftemperatur 960°C,

bzw. V-O nach UL 94, halogenfrei.

Klemmhöhe 9 mm - mit Distanzstück 13 mm.

Befestigungsloch 6 mm Ø.

2034 for max. 10 cables NYM 3 x 1.5 mm²



PA Polyamide

Master data

Item number	2204991
Type	2034 SP
Description 1	Pressure clip
Description 2	Large packaging
Manufacturer	OBO
Dimension	2x5 NYM3x1,5
Colour	Light grey; RAL 7035
Material	Polyamide
Smallest sales unit	100
Unit of quantity	Units
Weight	1,169 kg
Weight unit	kg/100 pairs

Technical specifications

No. of conductors NYM 3 x 1.5	10
Flame-resistant version	no
Maintain electrical functions	no
Halogen-free	yes
With anchor	no