

Technical data sheet

Pressure clip for 16 cables, connectable

Item number: 2205053



The quicker, the better – this also applies to installations in false ceilings. OBO pressure clips simplify the routing of cables under the ceiling. OBO pressure clip is the perfect installation partner for areas in which every centimetre counts. Mounting is carried out simply using an M6 knock-in anchor. The striking surface on the top guarantees high striking accuracy in the screw. After assembly, the cables are passed under the clips in a "lasso technique" hand movement – and that's all there is to it!

The pressure clip is made of high-quality polyamide.

2033 for max. 16 cables NYM 3 x 1.5 mm²



PA Polyamide

Master data

Item number	2205053
Type	2033 AS
Description 1	Pressure clip
Description 2	Connectable
Manufacturer	OBO
Dimension	2x8 NYM3x1,5
Colour	Light grey; RAL 7035
Material	Polyamide
Smallest sales unit	25
Unit of quantity	Units
Weight	2,1 kg
Weight unit	kg/100 pairs

Technical specifications

No. of conductors NYM 3 x 1.5	16
Flame-resistant version	no
Maintain electrical functions	no
Halogen-free	yes
With anchor	no