

Technical data sheet

Connector, Rd 8–10 mm with M10 thread

Item number: 5304008



- With bore hole 10.2 mm
- With thread M10
- Including pre-mounted nut M10 and serrated washer
- Conforms to the requirements according to DIN VDE 0185-305 (IEC 62305)

St	Steel
F	Hot-dip galvanised

Master data

Item number	5304008
Type	5000
Description 1	Connection terminal
Description 2	for round cable
Manufacturer	OBO
Dimension	8-10mm
Material	Steel
Surface	Hot galvanised
Surface standard	DIN 267, Teil 10
Smallest sales unit	20
Unit of quantity	Units
Weight	4,63 kg
Weight unit	kg/100 pairs

Technical specifications

Type of fastening screw	Miscellaneous
Type of connector	Connectors
Suitable for connection	Miscellaneous
Fit	Rd 8-10 mm
Intermediate plate	no