

# Technical data sheet

## Connector Rd 8–10 mm, single

Item number: 5304107



- With fix contact clamping screw, nut and serrated washer
- With bore hole 10.2 mm
- With pre-mounted pressure piece, die-cast zinc
- Conforms to the requirements according to DIN VDE 0185-305 (IEC 62305)

<b>St</b>	Steel
<b>FT</b>	Hot-dip galvanised

### Master data

Item number	5304107
Type	5001 DIN-FT+VA
Description 1	Connection terminal
Description 2	for round conductors w. VA nut
Manufacturer	OBO
Dimension	8-10mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	20
Unit of quantity	Units
Weight	7,45 kg
Weight unit	kg/100 pairs

### Technical specifications

Type of fastening screw	Clamping screw
Type of connector	Connectors
Lightning current carrying capacity	N/50 kA
Suitable for connection	Miscellaneous
Fit	Rd 8-10 mm

# Technical data sheet

Connector Rd 8–10 mm, single

Item number: 5304107



## Technical specifications

Intermediate plate	no
--------------------	----