

# Technical data sheet

## Connector, Rd 8–10 mm with pressure trough

Item number: 5304176



- With 1 fix contact clamping screw, nut and serrated washer
- Including pre-mounted pressure sump, steel
- Conforms to the requirements according to DIN VDE 0185-305 (IEC 62305)



**A2** Stainless steel

### Master data

|                     |                                   |
|---------------------|-----------------------------------|
| Item number         | 5304176                           |
| Type                | 5001 N-VA                         |
| Description 1       | Connection terminal               |
| Description 2       | for round cable                   |
| Manufacturer        | OBO                               |
| Dimension           | 8-10mm                            |
| Material            | Stainless steel, rustproof 1.4301 |
| Smallest sales unit | 10                                |
| Unit of quantity    | Units                             |
| Weight              | 6,8 kg                            |
| Weight unit         | kg/100 pairs                      |

### Technical specifications

|                                     |                                   |
|-------------------------------------|-----------------------------------|
| Type of fastening screw             | Clamping screw                    |
| Type of connector                   | Connectors                        |
| Lightning current carrying capacity | N/50 kA                           |
| Suitable for connection             | Round conductor Rd 8–10 / Rd 8–10 |
| Fit                                 | Rd 8-10 mm                        |
| Intermediate plate                  | no                                |