

# Technical data sheet

## Connection and end piece with connector and pressure trough

Item number: 5304660



- With 2 attaching holes Ø 11 mm
- Including pre-mounted connector 5001 N
- Conforms to the requirements according to DIN VDE 0185-305 (IEC 62305)



**St** Steel

**FT** Hot-dip galvanised

### Master data

Item number	5304660
Type	5005 N-FT
Description 1	Connection terminal
Description 2	with connecting strap
Manufacturer	OBO
Dimension	8-10mm
Material	Steel
Surface	Hot-dip galvanised
Surface standard	DIN EN ISO 1461
Smallest sales unit	10
Unit of quantity	Units
Weight	11,6 kg
Weight unit	kg/100 pairs

### Technical specifications

Type of fastening screw	Hex set screw
Type of connector	End piece
Lightning current carrying capacity	H/100 kA
Suitable for connection	Miscellaneous
Fit	Rd 8-10 mm

# Technical data sheet

Connection and end piece with connector and pressure trough

Item number: 5304660



## Technical specifications

Intermediate plate	no
--------------------	----