

# Technical data sheet


## Adjustable insulating beam – wall

Item number: 5408852



Variable spacer for cables and interception rods to maintain the separation distance.

- Infinitely adjustable distance range (L = 550–1,000 mm)
- Made of fibre glass-reinforced plastic (km = 0.7)
- For wall mounting with 10 4.2 mm fastening holes and 4 6.9 mm fastening holes

 Fibre-glass-reinforced plastic

### Master data

Item number	5408852
Type	ISAV1000W
Description 1	Insulated spacer
Description 2	variable length adjustment
Manufacturer	OBO
Dimension	550-1000mm
Material	Fibreglass-reinforced plastic
Smallest sales unit	1
Unit of quantity	Units
Weight	130 kg
Weight unit	kg/100 pairs