Technical data sheet

Empty housing X 10 with hat profile rail

Item number: 2005564





Junction box with hat profile rail for the connection of cables in indoor and outdoor areas. Rectangular design without entries. Suitable for wall and ceiling mounting with the option to fasten outside, inside or to mount via the corner domes. Particularly impact resistant with IK09. Transparent cover with quick lock, sealable. Made from halogen-free and UV-resistant materials.

With hat profile rail, type 2069, and fastening set.

Junction box according to DIN EN 60670. Impact resistance IK09 according to DIN EN 50102. Protection rating IP67 according to DIN EN 60529.



















Polycarbonate

М	_	_	4.		_	_	_	4-
IVI	ы	S	т	-1	г.	О	н	та

Item number	2005564
Туре	X10C R LGR-TR
Description 1	Empty Enclosure
Description 2	with trans. lid, rail 2069
Manufacturer	OBO
Dimension	190x150x125
Colour	Grey / transparent
Material	Polycarbonate
Smallest sales unit	1
Unit of quantity	Piece
Weight	65.6 kg
Weight unit	kg/100 pc.

Technical data sheet


Empty housing X 10 with hat profile rail





Dimensions 921

Length	191 mm
Width	151 mm
Height	126 mm



Technical data

Extension option Cover fastening Screwed Shape Square Suitable for outdoor use Clear internal dimensions ith lid yes Mounting type Protection rating Protection rating IK code Protection class Permitted temperature range, max. Permitted temperature range, min. Transparent lid Weatherproof Screwed Screwed Square Square Square Square yes UF7x137x110 mm yes Surface-mounted IK09 IK09 For C C Sor C S		
Shape Square Suitable for outdoor use yes Clear internal dimensions 177x137x110 mm with lid yes Mounting type Surface-mounted Protection rating IP67 Protection rating IK code IK09 Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid yes	Extension option	no
Suitable for outdoor use Clear internal dimensions Ves Clear internal dimensions Vith lid Ves Mounting type Protection rating Protection rating Ves Vith lid Ves	Cover fastening	Screwed
Clear internal dimensions with lid yes Mounting type Protection rating Protection rating IP67 Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid 177x137x110 mm yes Surface-mounted IK09 IK09 IK09 For C For C yes	Shape	Square
with lid yes Mounting type Surface-mounted Protection rating IP67 Protection rating IK code IK09 Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid yes	Suitable for outdoor use	yes
Mounting type Surface-mounted Protection rating IP67 Protection rating IK code IK09 Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid Surface-mounted Transparent Surface-mounted For Company IP67 Transparent Surface-mounted For Company IP67 For Company IR67 F	Clear internal dimensions	177x137x110 mm
Protection rating IP67 Protection rating IK code IK09 Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid IP67 IK09 IK09 IK09 IF07 IK09 IK09 IF07 IK09 IF07 IK09 IF07 IF07 IF07 IF07 IF07 IF07 IF07 IF07	with lid	yes
Protection rating IK code Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid IK09 II 60 °C 5 °C yes	Mounting type	Surface-mounted
Protection class II Permitted temperature range, max. Permitted temperature range, min. Transparent lid II 60 °C -5 °C yes	Protection rating	IP67
Permitted temperature range, max. Permitted temperature range, min. Transparent lid 60 °C -5 °C yes	Protection rating IK code	IK09
max. Permitted temperature range, min. Transparent lid yes	Protection class	II
min. Transparent lid yes	1 ,	60 °C
		-5 °C
Weatherproof yes	Transparent lid	yes
	Weatherproof	yes