

Technical data sheet

Screw-in beam clamp, with hinge

Item number: 1488111



Two-hinge beam clamp for fastening on beams without welding and drilling. The maximum load is dependent on the load direction.

CE

St	Steel
ZL	Zinc slat

Master data

Item number	1488111
Type	TK FL G
Description 1	Hinged support bracket
Description 2	Model "E"
Manufacturer	OBO
Dimension	0-24mm
Material	Steel
Surface	Zinc slat
Surface standard	
Smallest sales unit	10
Unit of quantity	Units
Weight	34 kg
Weight unit	kg/100 pairs

Technical data sheet

Screw-in beam clamp, with hinge

Item number: 1488111



Technical specifications

Connection type/component	Miscellaneous
Fastening type	Bolts
Breaking load	2,8 kN
Flange thickness F max.	24 mm
Flange thickness F min.	0 mm
Suitable for metric threaded rod	10
Thread metric	10
Hinge, adjustable	yes
Hinged	yes